Product data sheet 21.700

TUC: Universal thermostat

How energy efficiency is improved

Control, monitoring and limiting according to needs and with no auxiliary energy.

Features

- Regulates and monitors the temperature of liquids in baths, containers, pipes and ducts
- · Variants as temperature monitors (TW), safety temperature monitors (STW), temperature limiters (TB) or safety temperature limiters (STB)
- Thermostat with remote sensor
- · Clamp-on thermostat
- · Capillary tube thermostat with or without thermowell
- · Double thermostat, e.g. as TW and STB
- As per PED 97/23/EC (2014/68/EU) classified as cat. IV (TUC207F003 and TUC407F001)
- The shift in the change-over point is minimised due to the temperature compensation.
- 100 mm thermowell supplied.

Technical data

Power supply				
Max. load	Terminal 1-2	230 V~, 10 (2.5) A (on the normally closed contact)		
	Terminal 1-4	230 V~ 2 (0.4) A		
Parameters				
	Adjustment point	For t _a 22 °C		
	Effect of temperature at instrument head	Approx0.10.2 K/K		
	Time constant with thermowell (LW 7	l (LW 7) < 45 s (water) < 60 s (oil)		
	Time constant without thermowell	< 120 s (air)		
Ambient conditions				
	Ambient temperature	070 °C		
	Storage and transport temperature	-2580 °C		
Construction				
	Connection terminals	Plug-in connectors		
	Cable cross-section	0.752.5 mm ²		
	Sensor cartridge	Ø 6.5 mm		
	Housing	Two sections, lower section black, upper section yellow, including inspection window		
	Housing material	PA, ABS, PMMA		
	Weight	0.2 kg		
Standards and directives				
	Type of protection	IP54 (EN 60529)		
	Protection class	I (EN 60730)		
	Test marks	TÜV ID:0000046121		

Overview of type	es					
Туре	Setting range	Туре	Switching dif- ference	Capillary tube length	Thermowell	Max. sensor temp.
TUC101F003	-1050 °C	TW	Approx. 4.2 K	1.6 m	100 mm, brass	140 °C
TUC102F001	530 °C	TW	Approx. 5.6 K	0.7 m	100 mm, brass	200 °C
TUC105F001	1595 °C	TW	Approx. 5.6 K	0.7 m	100 mm, brass	200 °C
TUC106F001	40120 °C	TW	Approx. 5.6 K	0.7 m	100 mm, brass	200 °C
TUC107F001	50130 °C	TW	Approx. 5.6 K	0.7 m	100 mm, brass	200 °C
TUC108F001	80160 °C	TW	Approx. 5.6 K	0.7 m	100 mm, stain- less steel	200 °C
TUC207F003	70130 °C	STW	Approx. 10 K	1.6 m	100 mm, brass	160 °C




TUC*0*F00*



TW, STW



TB, STB







Product data sheet 21.700

Туре	Setting range	Туре	Switching dif- ference	Capillary tube length	Thermowell	Max. sensor temp.
TUC303F001	1560 °C	ТВ	≤ 20 K	0.7 m	100 mm, brass	200 °C
TUC307F001	50130 °C	ТВ	≤ 20 K	0.7 m	100 mm, brass	200 °C
TUC407F001	95130 °C	STB	≤ 20 K	0.7 m	100 mm, brass	160 °C

Only use the supplied thermowells or stainless-steel thermowells (part nos.: 0393022*** or 0392022***) with the TUC407F001 and TUC207F003.

Accessories	
Туре	Description
0300360008	Retaining holder for cable temperature sensor or capillary tube with 0392022*** (LW 7 or 15) (10 pieces)
0300360009	Holder for sensor cartridge
0300360010	Retaining strap for fitting onto pipes
0300360011	Mounting plate for double thermostats
0300360012	Sensor support spiral for fitting in ventilation duct
0300360013	Duct/wall mounting bracket

Description of operation

This universal thermostat regulates and monitors the temperature of liquids or air in baths, containers, pipes and ducts.

Definitions and functions

Depending on the temperature, the single-pole change-over switch is activated.

Setpoint (X_s)

The setpoint (X_s) , which can be adjusted, corresponds to the upper change-over point.

Switching difference (X_{sd})

The switching difference (X_{sd}) is equal to the difference between the upper and lower switching point. It is set to a fixed value for all TUC models (see type description).

Temperature monitor (TW)

The adjustment of the temperature setpoint is only possible with the aid of a tool. The set temperature is switched on and off automatically.

Safety temperature monitor (STW)

The STW has the same functions as the TW, but the contact switches to the safe side if a capillary tube is broken.

Temperature limiter (TB)

The adjustment of the temperature setpoint is only possible with the aid of a tool. The reset is initiated by pressing the RESET button with a tool once the temperature has decreased by the minimum switching difference.

Safety temperature limiter (STB)

The STB has the same functions as the TB, but the contact switches to the safe side if a capillary tube is broken. As it is classified as PED 97/23/EC cat. IV, the STB is suitable for safety applications.

Two universal housings can be connected to each other using accessory 0300360011. In this way, it is easy to create a monitor-limiter double thermostat.

Intended use

This product is only suitable for the purpose intended by the manufacturer, as described in the "Description of operation" section.


All related product regulations must also be adhered to. Changing or converting the product is not admissible.

Technical appendix

Switching point accuracy

Product data sheet 21.700

TW	STW, TB, STB
At the adjustment point ±6 K	At the adjustment point 0/-9 K



RC circuitry for inductive load

For the optimum RC circuitry, see the information from manufacturers of gates, relays, etc. If this is not available, the inductive load can be reduced by applying the following rule of thumb:

- Capacity of the RC circuitry (µF) equal to or greater than the operating current (A)
- Resistance of the RC circuitry (Ω) approx. the same as the resistance of the coil (Ω)

Materials

Material		
Housing base	PA	
Housing cover	ABS	
Inspection window	PMMA	
Thermowell (LW 7)	Brass (CuZn)	
	Stainless steel (CrNi)	

It is the responsibility of the operator to check and verify that the thermowell materials are compatible with the fluids in which they are submerged.

Sensor medium	
Up to 160 °C	Silicone oil


Based on the available information, when used as intended, the product is not dangerous as per Directive 67/548/EEC.

Disposal


When disposing of the product, observe the currently applicable local laws.

More information on materials can be found in the Declaration on materials and the environment for this product.

Connection diagram




21.700 Product data sheet




Note Use temperature-resistant cables (T > 90 °C)

Dimension drawing








21.700 Product data sheet

Accessories




[mm]




0300360012

[mm]




0300360013

[mm]




60 72,5





0300360009 [mm]





Fr. Sauter AG Im Surinam 55 CH-4016 Basel Tel. +41 61 - 695 55 55 www.sauter-controls.com